



Quiltec I Polyester Flat Mop Head

Two-ply 100% polyester flat mop head with synthetic core

Description

Quiltec I Polyester Mop Heads have been specifically designed for use with Contec's Mop Saturation System 2787. With high absorbency the mops are suitable for single use saturation, giving a surface coverage up to approximately 20 sq m. The mop head system is designed for hands-free fitting to the mop head frame.

The mop heads are compatible with the QuickTask hinged mop frame 2749.

The Quiltec I Polyester Mop Heads are constructed from a two-ply quilted 100% polyester on the outer face with a synthetic fibrefill core. This provides a highly sorbent mop head which is suitable for the application of disinfectants and removal of light soil, residues and biofilms. Designed for single use, the mop heads are compatible with a wide range of chemicals and disinfectants.

The MHQT0150 is provided sterile by gamma irradiated at no less than 25 kGy.

Technical Data

| Mop head component materials (cleaning surface first) | Two-ply 100% knitted polyester / synthetic fibrefill core | |
|---|---|----------------------------|
| Construction | Multi-layer sewn lamination | |
| Dimensions cm | 39 x 13cm nominal | |
| Attribute; (units) | Value ** | Test Method |
| Mop weight, dry; (g/mop) | 57 | CTM 004-03 |
| Sorbency in water (mL/mop) | 345 | CTM 004-03 |
| Non-volatile residue, NVR | | IEST-RP-CC004.2, Sec.6.1.2 |
| In deionized water; (g/mop) | 0.005 | |
| In isopropanol; (g/mop) | 0.010 | |
| Particles $\geq 0.5\mu\text{m}$; ($\times 10^6$ /mop) | 33.88 | IEST-RP-CC004.2, Sec.5.2 |
| Fibers $> 100\mu\text{m}$; ($\times 10^3$ /mop) | 3.60 | IEST-RP-CC004.2, Sec.5.2 |

** ND = None detected; levels are below detection limit of test equipment

| Part Number | Description | Packaging |
|-------------|--------------------------------------|------------------------------------|
| MHQT0100 | Quiltec I Polyester Mop Head | 5 per double bag / 8 bags per case |
| MHQT0150 | Quiltec I Polyester Mop Head Sterile | 5 per double bag / 8 bags per case |

Notes:

- 1) The information presented here is applicable to the part numbers shown above as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
- 2) Data shown are typical values and should not be used as product specifications.
- 3) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- 4) Current and/or comparison data may be available. Please contact a Contec sales representative for details.

Revision date: 06/03/2017
ETR002695



Copyright © 2017 Contec, Inc. All rights reserved.

North America
P.O. Box 530
Spartanburg, SC 29304 USA
Phone: +1-864-503-8333
www.contecinc.com

Europe
Zl du Prat – RP 3707
56037 VANNES Cedex
FRANCE
+33 297 437 690

China
No.17 Longyun Road
Suzhou 215024
CHINA
+ 86-512-6274 4050